

oil and dust remove ultrasonic cleaning machine for timing gears and screws

Our Product Introduction

Basic Information

- Place of Origin: China
- Brand Name: skymen
- Certification: CE/ROHS/ISO9001
- Model Number: JP-030S
- Minimum Order Quantity: 1 set
- Price: Negotiation
- Packaging Details: carton box
- Delivery Time: In Stock
- Payment Terms: L/C, T/T, Paypal
- Supply Ability: 500 sets per day



Product Specification

- Material: Stainless Steel
- Clean Medium: Wet Cleaning
- Customize: Available
- Theory: Physical Cleaning
- Cleaning Effect: Thorough Cleaning
- Status: New
- Highlight: **ultrasonic bath cleaner,
ultrasonic cleaning equipments**

Product Description

4.5L optic lens and glass cleaning solution ultrasonic cleaner



Features:

Upgrade Sereies with **Degas** to speed up the cleaning progress. The “**Degas**” function accelerates the degassing process in the liquid in a very efficient way.

Weak and strong cleaning model for opiton;

Stainless steel tank has resistance to wear and long work life.

Powerful industrial transducer output ;

For varies appliance: Jewelery ,watch ,razor ,glass options

Specification:

Model	JP-030S
Ultrasonic power	180W (3pc transducer)
Frequency	40KHz
Housing material	SUS304
Tank material	SUS304
Heating power	200W
Tank capacity	4.5 L
Timer	Digital 1-30 min adjustable
Heater	20~80°C
Function	Degas, Semi-wave
Voltage	AC 100~120V, 60Hz AC 220~240V, 50Hz
Tank size	300*150*100 mm
Unit size	325*180*225 mm
Packing size	410*255*310mm
N.W.	4.6 Kg
G.W.	5.4 Kg
Certificate	RoHs / CE

Details of product :

PRODUCT PHOTO

1

Angle of 45-degrees display

Glasses/Ijector/Hardware parts/Circuit Board/Laboratory/Dentistry



SAFE

Just get used to the details



High quality
silicone pad
stable



Industrial-grade
power cord
safe



Stainless steel
mesh basket,
solid and durable



Matt surface
treatment,
anti-scratch




Ground plug
and power switch,
secure

SKYMEN COORDINATOR


Use high-quality core

Skymen Coordinator



Adopt high-quality components distribute power evenly, all transducers work at one frequency vibration point, which achieve a powerful resonance effect, delivery a uniform and thorough cleaning performances.

Other Coordinator



Current and power are uncontrolled, weak resonance effect, normal cleaning performance.


Why ultrasonic cleaner ?

Specially designed transducers transform electric energy into mechanical vibrations. These are transmitted into the cleaning liquid, creating many tiny vacuum-filled bubbles which rapidly implode. This process, called cavitation, releases highly energetic jets of liquid which remove all kinds of contamination from metal, glass, and plastic surfaces. Every surface that comes in contact with the fluid is thoroughly cleaned.

Application :

Auto part and machinery parts,
Lab and medical instruments;
Die casting and injection module;
All metal / plastic parts are suitable for ultrasonic cleaner .

COMPARISON OF CLEANING EFFECT



Skymen Technology Corporation Limited

☎ 86-755-27094405

✉ info@skymen.cc

🌐 skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen